



FEATURES


- Small size; just under 2" diameter, about 9/16" high
- Exclusive IMS™ Interchangeable mount allows you to A/B test different exciters
- · Rare-earth neodymium motor and a proprietary voice coil
- 1" voice coil for 20 watt RMS power handling

APPLICATIONS

- Electronic gaming machines
- Advertising signage
- Point-of-purchase displays
- Multimedia exhibits
- · Commercial distributed audio
- Kiosks
- Automotive audio







 $1/3^{rd}$ octave smoothing - measurement taken with transducer adhered off-center on a 12" x 12" x 1/2" foam core board in an infinite baffle setup.

Note: This information is for comparison purposes only, the actual frequency response will depend on many factors of which the diaphragm being the greatest contributor.